



**Part Number :** [1301460063](#)

**Product Description :** Watertite Extreme Ground Fault Monitoring Connector 2 Pole/3 Wire, NEMA 5-15, 125V, Cord Grip Body Size F2, Silicone Husk

**Series Number :** 130146

**Status :** Active

**Product Category :** Wiring Devices

**Engineering Number :** 15W47GCM



---

## Documents & Resources

### Drawings

[Drawing 1301460063\\_sd.pdf](#)

### 3D Models and Design Files

[3D Model 1301460063\\_stp.zip](#)

---

## Product Environment Compliance

### Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

### [Multiple Part Product Compliance Statements](#)

- Eu RoHS
- REACH SVHC
- Low-Halogen

### [Multiple Part Industry Compliance Documents](#)

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474

## Part Details

### General

Status	Active
Category	Wiring Devices
Series	130146
Description	Watertite Extreme Ground Fault Monitoring Connector 2 Pole/3 Wire, NEMA 5-15, 125V, Cord Grip Body Size F2, Silicone Husk
IP Rating	IP69K
NEMA Configuration	NEMA 5-15
Product Family	Watertite Extreme Wet-Location Wiring Solutions
Product Name	Watertite Extreme
Specialty	Monitoring
Type	Connector
UPC	78678805848

### Agency

CSA	LR6837
UL	E10176

### Electrical

Current - Maximum per Contact	15.0A
GFCI	No
Voltage - Maximum	125V

### Physical

Cord Grip Body Size	F2 1/2"
Cord Type	N/A
Flange	No
Flip Lid	No
Gender	Female

Length	N/A
Lighted Connector	Yes
Locking Blade	No
Poles	2-pole/3-wire
Receptacle Type	Single

---

This document was generated on Sep 26, 2023