



Part Number : [1301460128](#)

Product Description : Watertite Extreme Receptacle with Duplex Flip Coverplate, 2 Pole/3 Wire, NEMA 7-15, 277V

Series Number : 130146

Status : Active

Product Category : Wiring Devices

Engineering Number : 60W34DPLX



---

## Documents & Resources

### Drawings

[Drawing 1301460128\\_sd.pdf](#)

### 3D Models and Design Files

[3D Model 1301460128\\_stp.zip](#)

---

## Product Environment Compliance

### Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

### [Multiple Part Product Compliance Statements](#)

- Eu RoHS
- REACH SVHC
- Low-Halogen

### [Multiple Part Industry Compliance Documents](#)

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

## Part Details

### General

Status	Active
Category	Wiring Devices
Series	130146
Description	Watertite Extreme Receptacle with Duplex Flip Coverplate, 2 Pole/3 Wire, NEMA 7-15, 277V
IP Rating	IP67
NEMA Configuration	NEMA 7-15
Product Family	Watertite Extreme Wet-Location Wiring Solutions
Product Name	Watertite Extreme
Specialty	N/A
Type	Receptacle
UPC	78678871433

### Agency

CSA	LR6837
UL	E68122

### Electrical

Current - Maximum per Contact	15.0A
GFCI	No
Voltage - Maximum	277V

### Physical

Cord Type	N/A
Flange	No
Flip Lid	Yes
Gender	Female
Length	N/A
Lighted Connector	No
Locking Blade	No

Poles	2-pole/3-wire
Receptacle Type	Single

---

This document was generated on Sep 26, 2023