



Part Number : [1301460145](#)

Product Description : Watertite Extreme Receptacle Single Flip Coverplate with Locking Blade, 3 Pole/3 Wire, Non-NEMA 15A/125V, 10A/250V

Series Number : 130146

Status : Active

Product Category : Wiring Devices

Engineering Number : 65W07



---

## Documents & Resources

### Drawings

[Drawing 1301460145\\_sd.pdf](#)

### 3D Models and Design Files

[3D Model 1301460145\\_stp.zip](#)

---

## Product Environment Compliance

### Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

### [Multiple Part Product Compliance Statements](#)

- Eu RoHS
- REACH SVHC
- Low-Halogen

### [Multiple Part Industry Compliance Documents](#)

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

## Part Details

### General

Status	Active
Category	Wiring Devices
Series	130146
Description	Watertite Extreme Receptacle Single Flip Coverplate with Locking Blade, 3 Pole/3 Wire, Non-NEMA 15A/125V, 10A/250V
IP Rating	IP67
NEMA Configuration	Non-NEMA Locking
Product Family	Watertite Extreme Wet-Location Wiring Solutions
Product Name	Watertite Extreme
Specialty	N/A
Type	Receptacle
UPC	78678871580

### Agency

UL	E68122
----	--------

### Electrical

Current - Maximum per Contact	10.0A, 15.0A
GFCI	No
Voltage - Maximum	125V / 250V

### Physical

Cord Type	N/A
Flange	No
Flip Lid	Yes
Gender	Female
Length	N/A
Lighted Connector	No
Locking Blade	Yes

Poles	3-pole/3-wire
Receptacle Type	Single

---

---

This document was generated on Sep 26, 2023