



Part Number : [1301460146](#)

Product Description : Watertite Extreme Receptacle Duplex Flip Coverplate with Locking Blade, 3 Pole/3 Wire, Non-NEMA 15A/125V, 10A/250V

Series Number : 130146

Status : Active

Product Category : Wiring Devices

Engineering Number : 65W07DPLX



Documents & Resources

Drawings

[Drawing 1301460146_sd.pdf](#)

3D Models and Design Files

[3D Model 1301460146_stp.zip](#)

Product Environment Compliance

Compliance

| | |
|--------------------|--------------|
| China RoHS | Not Reviewed |
| EU ELV | Not Reviewed |
| Low-Halogen Status | Not Reviewed |
| REACH SVHC | Not Reviewed |
| EU RoHS | Not Reviewed |

[Multiple Part Product Compliance Statements](#)

- Eu RoHS
- REACH SVHC
- Low-Halogen

[Multiple Part Industry Compliance Documents](#)

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Part Details

General

| | |
|--------------------|--|
| Status | Active |
| Category | Wiring Devices |
| Series | 130146 |
| Description | Watertite Extreme Receptacle Duplex Flip Coverplate with Locking Blade, 3 Pole/3 Wire, Non-NEMA 15A/125V, 10A/250V |
| IP Rating | IP67 |
| NEMA Configuration | Non-NEMA Locking |
| Product Family | Watertite Extreme Wet-Location Wiring Solutions |
| Product Name | Watertite Extreme |
| Specialty | N/A |
| Type | Receptacle |
| UPC | 78678871441 |

Agency

| | |
|-----|--------|
| CSA | LR6837 |
| UL | E68122 |

Electrical

| | |
|-------------------------------|--------------|
| Current - Maximum per Contact | 10.0A, 15.0A |
| GFCI | No |
| Voltage - Maximum | 125V / 250V |

Physical

| | |
|-------------------|--------|
| Cord Type | N/A |
| Flange | No |
| Flip Lid | Yes |
| Gender | Female |
| Length | N/A |
| Lighted Connector | No |

| | |
|-----------------|---------------|
| Locking Blade | Yes |
| Poles | 3-pole/3-wire |
| Receptacle Type | Duplex |

This document was generated on Sep 26, 2023