



Part Number : [1301460153](#)

Product Description : Watertite Extreme Receptacle with Single Flip Coverplate with Locking Blade, 2 Pole/3 Wire, NEMA L6-15, 250V

Series Number : 130146

Status : Active

Product Category : Wiring Devices

Engineering Number : 65W49



Documents & Resources

Drawings

[Drawing 1301460153_sd.pdf](#)

3D Models and Design Files

[3D Model 1301460153_stp.zip](#)

Product Environment Compliance

Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

[Multiple Part Product Compliance Statements](#)

- Eu RoHS
- REACH SVHC
- Low-Halogen

[Multiple Part Industry Compliance Documents](#)

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474

Part Details

General

Status	Active
Category	Wiring Devices
Series	130146
Description	Watertite Extreme Receptacle with Single Flip Coverplate with Locking Blade, 2 Pole/3 Wire, NEMA L6-15, 250V
IP Rating	IP67
NEMA Configuration	NEMA L6-15
Product Family	Watertite Extreme Wet-Location Wiring Solutions
Product Name	Watertite Extreme
Specialty	N/A
Type	Receptacle
UPC	78678870089

Agency

CSA	LR6837
UL	E68122

Electrical

Current - Maximum per Contact	15.0A
GFCI	No
Voltage - Maximum	250V

Physical

Cord Type	N/A
Flange	No
Flip Lid	Yes
Gender	Female
Length	N/A

Lighted Connector	No
Locking Blade	Yes
Poles	2-pole/3-wire
Receptacle Type	Single

This document was generated on Sep 26, 2023