



**Part Number :** [1301470045](#)

**Product Description :** Watertite Extreme Extra-Hard Outdoor Use Connector with Locking Blade, 2 Pole/3 Wire, NEMA L5-20, 125V, Cord Grip Body Size F3

**Series Number :** 130147

**Status :** Active

**Product Category :** Wiring Devices

**Engineering Number :** 27W47BLK



---

## Documents & Resources

### Drawings

[Drawing 1301470045\\_sd.pdf](#)

### 3D Models and Design Files

[3D Model 1301470045\\_stp.zip](#)

---

## Product Environment Compliance

### Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

### [Multiple Part Product Compliance Statements](#)

- Eu RoHS
- REACH SVHC
- Low-Halogen

### [Multiple Part Industry Compliance Documents](#)

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

## Part Details

### General

Status	Active
Category	Wiring Devices
Series	130147
Description	Watertite Extreme Extra-Hard Outdoor Use Connector with Locking Blade, 2 Pole/3 Wire, NEMA L5-20, 125V, Cord Grip Body Size F3
IP Rating	IP67
NEMA Configuration	NEMA L5-20
Product Family	Watertite Extreme Wet-Location Wiring Solutions
Product Name	Watertite Extreme
Specialty	N/A
Type	Connector
UPC	78678871474

### Agency

CSA	LR6837
UL	E10176

### Electrical

Current - Maximum per Contact	20.0A
GFCI	No
Voltage - Maximum	125V

### Physical

Cord Grip Body Size	F3 3/4"
Cord Type	N/A
Flange	No
Flip Lid	No
Gender	Female
Length	N/A

Lighted Connector	No
Locking Blade	Yes
Poles	2-pole/3-wire
Receptacle Type	Single

---

This document was generated on Sep 26, 2023