



Part Number : [1301470153](#)

Product Description : Watertite Extreme Receptacle with Locking Blade, Single Flip Coverplate, 4 Pole/5 Wire, NEMA L22-20, 3ø 480V

Series Number : 130147

Status : Active

Product Category : Wiring Devices

Engineering Number : 67W82



---

## Documents & Resources

### Drawings

[Drawing 1301470153\\_sd.pdf](#)

### 3D Models and Design Files

[3D Model 1301470153\\_stp.zip](#)

---

## Product Environment Compliance

### Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

### Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

### Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474

## Part Details

### General

Status	Active
Category	Wiring Devices
Series	130147
Description	Watertite Extreme Receptacle with Locking Blade, Single Flip Coverplate, 4 Pole/5 Wire, NEMA L22-20, 3Ø 480V
IP Rating	IP67
NEMA Configuration	NEMA L22-20
Product Family	Watertite Extreme Wet-Location Wiring Solutions
Product Name	Watertite Extreme
Specialty	N/A
Type	Receptacle
UPC	78678871573

### Agency

UL	E68122
----	--------

### Electrical

Current - Maximum per Contact	20.0A
GFCI	No
Voltage - Maximum	3Ø 480V

### Physical

Cord Type	N/A
Flange	No
Flip Lid	Yes
Gender	Female
Length	N/A
Lighted Connector	No

Locking Blade	Yes
Poles	4-pole/5-wire
Receptacle Type	Single

---

This document was generated on Sep 26, 2023