



Part Number : [1301470174](#)

Product Description : Watertite Extreme Receptacle with Locking Blade, Single Flip Coverplate, 3 Pole/4 Wire, NEMA L15-30, 3ø 250V

Series Number : 130147

Status : Active

Product Category : Wiring Devices

Engineering Number : 69W75



Documents & Resources

Drawings

[Drawing 1301470174_sd.pdf](#)

3D Models and Design Files

[3D Model 1301470174_stp.zip](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Reviewed per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2023)3788-DC (14 Jun 2023)
EU RoHS	Not Reviewed per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration

- IEC-62474

- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Wiring Devices
Series	130147
Description	Watertite Extreme Receptacle with Locking Blade, Single Flip Coverplate, 3 Pole/4 Wire, NEMA L15-30, 3Ø 250V
IP Rating	IP67
NEMA Configuration	NEMA L15-30
Product Family	Watertite Extreme Wet-Location Wiring Solutions
Product Name	Watertite Extreme
Specialty	N/A
Type	Receptacle
UPC	78678871578

Agency

UL	E68122
----	--------

Electrical

Current - Maximum per Contact	30.0A
GFCI	No
Voltage - Maximum	3Ø 250V

Physical

Cord Type	N/A
Flange	No
Flip Lid	Yes
Gender	Female
Length	N/A

Lighted Connector	No
Locking Blade	Yes
Net Weight	65.440/g
Poles	3-pole/4-wire
Receptacle Type	Single

This document was generated on Sep 26, 2023