



Part Number : [1301490041](#)

Product Description : Safeway Flanged Receptacle with Locking Blade, 2 Pole/3 Wire, NEMA L7-20, 277V

Series Number : 130149

Status : Active

Product Category : Wiring Devices

Engineering Number : 2749MB



Product Environment Compliance

Compliance

| | |
|--------------------|--------------|
| China RoHS | Not Reviewed |
| EU ELV | Not Reviewed |
| Low-Halogen Status | Not Reviewed |
| REACH SVHC | Not Reviewed |
| EU RoHS | Not Reviewed |

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

| | |
|----------|----------------|
| Status | Active |
| Category | Wiring Devices |

| | |
|--------------------|--|
| Series | 130149 |
| Description | Safeway Flanged Receptacle with Locking Blade, 2 Pole/3 Wire, NEMA L7-20, 277V |
| IP Rating | N/A |
| NEMA Configuration | NEMA L7-20 |
| Product Family | Heavy-Duty Industrial Wiring Devices |
| Product Name | Safeway |
| Specialty | N/A |
| Type | Receptacle |
| UPC | 78678801757 |

Electrical

| | |
|-------------------------------|-------|
| Current - Maximum per Contact | 20.0A |
| GFCI | No |
| Voltage - Maximum | 277V |

Physical

| | |
|-------------------|---------------|
| Cord Type | N/A |
| Flange | Yes |
| Flip Lid | No |
| Gender | Female |
| Length | N/A |
| Lighted Connector | No |
| Locking Blade | Yes |
| Poles | 2-pole/3-wire |
| Receptacle Type | Single |