



Part Number : 1301510024

Product Description : Super-Safeway Adapter
NEMA L5-20 Receptacle - Female End
20A/125V, NEMANEMA 5-20 Plug - Male End,
20A/125V

Series Number : 130151

Status : Active

Product Category : Wiring Devices

Engineering Number : 1741



Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Reviewed per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2023)3788-DC (14 Jun 2023)
EU RoHS	Not Reviewed per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Wiring Devices
Series	130151
Description	Super-Safeway Adapter NEMA L5-20 Receptacle - Female End 20A/125V, NEMANEMA 5-20 Plug - Male End, 20A/125V
IP Rating	N/A
NEMA Configuration	NEMA L5-20
Product Family	Heavy-Duty Industrial Wiring Devices
Product Name	Super-Safeway
Specialty	N/A
Type	Adapter
UPC	78678875281

Agency

CSA	LR6837
UL	E10176

Electrical

Current - Maximum per Contact	60.0A
GFCI	No
Voltage - Maximum	125V

Physical

Cord Type	N/A
Flange	No
Flip Lid	No
Gender	Male
Length	N/A
Lighted Connector	No
Locking Blade	Yes
Net Weight	89.890/g
Poles	2-pole/3-wire
Receptacle Type	N/A

This document was generated on Sep 26, 2023