



Part Number : 1301540037

Product Description : Super-Safeway Inline GFCI Molded W Cordset, 2 Pole/3 Wire SJOW Cordset, Cordset Length 0.91m (3.0'), NEMA 5-15, 125V

Series Number : 130154

Status : Active

Product Category : Wiring Devices

Engineering Number : 1447-W-IN



Product Environment Compliance

Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Wiring Devices

Series	130154
Description	Super-Safeway Inline GFCI Molded W Cordset, 2 Pole/3 Wire SJOW Cordset, Cordset Length 0.91m (3.0'), NEMA 5-15, 125V
IP Rating	N/A
NEMA Configuration	NEMA 5-15
Product Family	Heavy-Duty Industrial Wiring Devices
Product Name	Super-Safeway
Specialty	N/A
Type	Molded W Cordset
UPC	78678838043

Electrical

Current - Maximum per Contact	15.0A
GFCI	Yes-In-line
Voltage - Maximum	125V

Physical

Cord Type	12/3 SJOW
Flange	No
Flip Lid	No
Gender	Male-Female
Length	0.91m (3.0')
Lighted Connector	No
Locking Blade	No
Poles	2-pole/3-wire
Receptacle Type	Triple