



Part Number : [1301540052](#)

Product Description : Watertite Extreme Standard Molded Y Cordset, 2 Pole/3 Wire, Cordset Length 0.91m (3.0'), NEMA 6-20, 250V

Series Number : 130154

Status : Active

Product Category : Wiring Devices

Engineering Number : 14W48-Y



---

## Documents & Resources

### Drawings

[Drawing 1301540052\\_sd.pdf](#)

---

## Product Environment Compliance

### Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

### Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

### Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

### EU RoHS Certificate of Compliance

---

## Part Details

### General

Status	Active
Category	Wiring Devices
Series	130154
Description	Watertite Extreme Standard Molded Y Cordset, 2 Pole/3 Wire, Cordset Length 0.91m (3.0'), NEMA 6-20, 250V
IP Rating	IP67
NEMA Configuration	NEMA 6-20
Product Family	Watertite Extreme Wet-Location Wiring Solutions
Product Name	Watertite Extreme
Specialty	N/A
Type	Molded Y Cordset
UPC	78678800610

### Agency

CSA	LL52750
-----	---------

### Electrical

Current - Maximum per Contact	20.0A
GFCI	No
Voltage - Maximum	250V

### Physical

Cord Grip Body Size	F2 1/2"
Cord Type	12/3 SOOW
Flange	No
Flip Lid	No
Gender	Male-Female
Length	0.91m (3.0')
Lighted Connector	No
Locking Blade	No
Poles	2-pole/3-wire

Receptacle Type	Duplex
-----------------	--------

---

This document was generated on Sep 26, 2023