



Part Number : [1301550110](#)

Product Description : Watertite Extreme Duplex GFCI Receptacle, 2 Pole/3 Wire, NEMA L5-20, 125V

Series Number : 130155

Status : Active

Product Category : Wiring Devices

Engineering Number : 67W47GF



Documents & Resources

Drawings

[Drawing 1301550110_sd.pdf](#)

Product Environment Compliance

Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Wiring Devices
Series	130155
Description	Watertite Extreme Duplex GFCI Receptacle, 2 Pole/3 Wire, NEMA L5-20, 125V
IP Rating	IP67
NEMA Configuration	NEMA L5-20
Product Family	Watertite Extreme Wet-Location Wiring Solutions
Product Name	Watertite Extreme
Specialty	N/A
Type	Receptacle
UPC	78678821627

Electrical

Current - Maximum per Contact	20.0A
GFCI	Yes - Receptacle
Voltage - Maximum	125V

Physical

Cord Type	N/A
Flange	No
Flip Lid	Yes
Gender	Female
Length	N/A
Lighted Connector	No
Locking Blade	Yes
Net Weight	1658.332/g
Poles	2-pole/3-wire
Receptacle Type	Single
