



Part Number : [5601230202](#)
Product Description : DuraClik ISL Wire-to-Board Receptacle Housing, Single Row, Red, 2 Circuits
Series Number : 560123
Status : Active
Product Category : Connector Housings



Documents & Resources

Drawings
[Drawing 5601230202_sd.pdf](#)

3D Models and Design Files
[3D Model 5601230202_stp.zip](#)

Specifications
[Packaging Specification PK-560123-001-001.pdf](#)
[Product Specification PS-560123-001-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Duty-To-Declare
China RoHS	
EU ELV	Compliant per 2000/53/EC
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2023)3788-DC (14 Jun 2023)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements
- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents
- IPC 1752A Class C
- IPC 1752A Class D

- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Connector Housings
Series	560123
Description	DuraClik ISL Wire-to-Board Receptacle Housing, Single Row, Red, 2 Circuits
Application	Automotive, Signal, Wire-to-Board
Product Family	DuraClik Connector System
Product Name	DuraClik
UPC	889056616904

Agency

UL	E29179
----	--------

Physical

Circuits (maximum)	2
Color - Resin	Red
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Resin	PBT
Net Weight	0.186/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	2.00mm
Polarized to Mating Part	Yes
Stackable	No

Temperature Range - Operating	-40° to +130°C
-------------------------------	----------------

Mates With / Use With

Mates with Part(s)

Description	Part Number
DuraClik Right-Angle Single Row Headers	<u>502352</u>
DuraClik Vertical Single Row Headers	<u>560020</u>

Use with Part(s)

Description	Part Number
DuraClik ISL Wire-to-Board Terminal Position Assurance (TPA) Retainer, 2 Circuits, Gray	/content/molex/molex-dot-com/us/en/products/product-page.html/5601250200.html
DuraClik ISL Female Crimp Terminals	<u>560124</u>