

Part Number: 354189002

Product Description: MP-Lock Quick

Disconnect with Vibration Support, Flag Type, Metal Strip, Tab 2.79 x 0.51mm, Pre-Tin

Plated

Series Number: 35418

Status: New Business Not Supported **Product Category:** Quick Disconnects



Documents & Resources

Tooling Specifications

Crimp Specification CS-35418-001-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	©
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2023)3788-DC (14 Jun 2023)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	New Business Not Supported
Category	Quick Disconnects
Series	35418
Description	MP-Lock Quick Disconnect with Vibration Support, Flag Type, Metal Strip, Tab 2.79 x 0.51mm, Pre-Tin Plated
Product Family	Standard Quick-Disconnect Terminals
Product Name	MP-Lock
Туре	Quick Disconnect
UPC	800753968455

Agency

UL	E92853

Electrical

Voltage - Maximum	300V
-------------------	------

Physical

Barrel Type	Open
Gender	Female
Glow-Wire Capable	No
Insulated	No
Insulation	None
Lock to Mating Part	Yes
Material - Metal	Brass
Net Weight	0.413/g
Orientation	Flag
Packaging Type	Reel
Polarized to Mating Part	No
Tab Thickness	0.51mm
Tab Width	4.75mm
Temperature Range - Operating	-40° to +105°C

Termination Interface Style	Crimp or Compression
Wire Size (AWG)	16, 18, 20, 22

This document was generated on Sep 26, 2023