



Part Number : [1200698600](#)
Product Description : Micro-Change (M12)
Single-Ended Cordset with Knurled Hexnut, 8
Poles, Female (Straight) to Pigtail, 24 AWG,
Black TPU WSOR Cable, 2.0m (6.56') Length
Series Number : 120069
Status : Active
Product Category : Circular Industrial
Cordsets
Engineering Number : 808S00BS2M020



Documents & Resources

Drawings
[Drawing 1200698600_sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2022)9120-DC (17 Jan 2023)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474

- chemSHERPA (xml)

EU RoHS Certificate of Compliance

ZZCERT_UKCA - Declaration of Conformity : CER_4000410299_00_000.pdf

ZZCERT_CE - Declaration of Conformity : CER_4000410038_00_000.pdf

Part Details

General

Status	Active
Category	Circular Industrial Cordsets
Series	120069
Description	Micro-Change (M12) Single-Ended Cordset with Knurled Hexnut, 8 Poles, Female (Straight) to Pigtail, 24 AWG, Black TPU WSOR Cable, 2.0m (6.56') Length
IP Rating	IP67
Product Family	Brad M8 and M12 Cordsets with Knurled Hexnuts and WSOR Cable
Product Name	Micro-Change (M12)
Protocol	N/A
Region	Europe
Type	Single Ended
UPC	889056131216

Agency

UL	E152210
----	---------

Electrical

Current - Maximum per Contact	2.0A
Voltage - Maximum	30V

Physical

Cable Diameter	6.90mm (.272")
Cable Length	2.0m (6.56')
Color - Cable Jacket	Black
Connector End A	Micro-Change (M12)
Connector End B	Pigtail

Coupling Style	Knurled Hexnut, Threaded
Gender	Female-Pigtail
Keyway	Single
LED Indicator	No
Material - Cable Jacket	TPU
Material - Connector Body	TPU
Material - Contact	Brass
Material - Coupling Nut	Nickel-plated Brass
Material - O-Ring	Fluoro-elastomer
Material - Plating Mating	Gold
Net Weight	161.800/g
Orientation	Straight to Pigtail
Poles	8
Temperature Range - Operating	-25° to +85°C
Wire/Cable Type	UL 21215
Wire Size (AWG)	24