



Part Number : [196001302](#)
Product Description : Avikrimp Quick Disconnect, Female, Fully Insulated, Tab 4.75 x 0.51mm, Loose
Series Number : 19600
Status : Active
Product Category : Quick Disconnects
Engineering Number : P-5239



Documents & Resources

Drawings

[Drawing 196001302_sd.pdf](#)

3D Models and Design Files

[3D Model 196001302_stp.zip](#)

Specifications

[Product Specification PS-19902-014-001.pdf](#)

[Product Specification PS-19902-013-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2023)3788-DC (14 Jun 2023)
EU RoHS	Compliant per EU 2015/863

[Multiple Part Product Compliance Statements](#)

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Quick Disconnects
Series	19600
Description	Avikrimp Quick Disconnect, Female, Fully Insulated, Tab 4.75 x 0.51mm, Loose
Product Family	Standard Quick-Disconnect Terminals
Product Name	Avikrimp
Type	Quick Disconnect
UPC	800753117785

Agency

CSA	LR18689
UL	E79133

Electrical

Voltage - Maximum	300V
-------------------	------

Physical

Barrel Type	Closed
Color - Resin	Yellow
Flammability	94V-2
Gender	Female
Glow-Wire Capable	No
Insulated	Fully
Insulation	Nylon (PA)

Lock to Mating Part	None
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	1.300/g
Orientation	Straight
Packaging Type	Bag
Polarized to Mating Part	No
Tab Thickness	0.51mm
Tab Width	4.75mm
Temperature Range - Operating	-65° to +105°C
Wire Insulation Diameter	6.89x4.32mm max.
Wire Size (AWG)	16+16, 18+18, 20+20, 22+22

Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

Application Tooling

Global

Description	Part Number
Hand Crimp Tool	<u>0640017100</u>
Air Powered Crimp Tool Head	<u>0640057100</u>