

BU-2323-10-XX-@

(Stackable, Retractable 4mm Banana Plugs, 10 AWG Silicone Jacket Wire)



- Mueller's BU-2323-10 has banana plugs that are rear stackable and have high force springs for better retention. They also have a spring loaded clear retractable sheath that provides electrical protection when the cable is not mounted.
- Wire used is 10 AWG Silicone wire, 1064 strand 56/08x19C, tinned copper with a highly flexible, 0.197" (5mm) diameter jacket.
- Ratings: Current 45 Amps
 Voltage Hands-free testing to 600V
- The "XX" in the part number indicates length in inches. Standard lengths: 6", 12", 18", 24", 36", 48", 60", 72", 79", 120"
- Color: The "@" in the part number represents color. Available colors: -0 Black, -2 Red, -4 Yellow, -5 Green, -6 Blue, -8 Gray, -9 White
- RoHS 3 compliant