

BU-26106-*

(UL® Listed Test Probe with 8-32 thread, Banana Connection)



- Insulated Plug-On test probe. Mounts to a test lead that has a 4mm shrouded, unshrouded, or retractable Banana plug. The 8-32 thread allows standard accessories (like the BU-60 TBO) to be mounted to the probe
- Size:
 - Probe Tip is a standard .080φ (2mm)
 - Probe Thread is 8-32 UNC
 - Overall Length is 3.3" (83mm)
 - Housing Diameter is .25" (6.4mm)
- Material:
 - Probe Tip: Stainless Steel
 - Housing: Nylon
- Ratings: 1000 V Cat III; 10 Amps.
- Colors: Designated by "*" in part number. Available options:
 - -0 Black; -2 Red; -4 Yellow; -5 Green; -6 Blue; -9 White
- RoHS Compliant, CE Certified