

BU-5030-C-XX-0

(BNC Male with RG58 to Insulated Alligator Clips)



- Mueller's BU-5030-C is a male BNC to two insulated alligator clips on a RG58 cable.
- Uses 20 AWG (41/36) tinned copper with 105°C PVC insulation, coaxial cable, shielded RG58C/U, MIL-C-17F.
- Material:

BNC shell	Tarnish-resistant plated brass
BNC center contact	Gold-plated brass
Alligator clips	Nickel-plated steel w/ PVC insulator
- Ratings:

Wire Impedance	50 Ohms
Current	5 Amps
Voltage	Hands-free testing to 300 VRMS
- The "XX" in the model number indicates length.

Available lengths:	12", 24", 36", 60"
--------------------	--------------------
- RoHS 3 compliant