

BU-P3285**(BNC "T" Adapter Female-Male-Female)**

- Mueller's BU-P3285 is a female-male-female BNC adapter.
- Material:

Body	Nickel-plated brass
Female contact	Gold-plated beryllium copper
Male contact	Gold-plated brass
Dielectric	PTFE
- Rating:

Voltage	30VAC/60VDC Max, 500 VRMS Max.
Temperature	-65°C (-85°F) to 165°C (329°F)
Impedance	50 Ohms
- RoHS 3 Compliant