

Item no.: 2924114 – Silver  
2924115 – Black

## Data Sheet

---

Turning knob aluminium ( $\varnothing$  x H): 23 mm x 13 mm  
Inner bore dia.: 6.0 mm



### Technical data

Turning knob size ( $\varnothing$  x H): 23 mm x 13 mm

Inner bore diameter: 6 mm

Material: Aluminum & plastic

Operating & Storage temperature: -25 °C ~ +85 °C

Operating & Storage humidity: 20 %RH ~ 85 %RH

### Drawing:

