

Incl. free
VitaDock+
app

- ✓ Faster measurement results thanks to inflation technology – The blood pressure is measured during the inflation of the cuff
- ✓ Accurate blood pressure measurement on the upper arm with blood pressure classification
- ✓ Ultra slim design in pocket-size

Upper arm blood pressure monitor BU 570 connect White

Art. Nr. 51203 | EAN 40 15588 51203 2



Measurements classified using a traffic-light scale

APPLICATION | FEATURES

- Bluetooth® data transfer to the VitaDock+ app for iOS and Android and to VitaDock® Online
- Large LCD display: 7.3 x 6 cm with backlight
- 120 memory slots for each of 2 users
- Calculates average value of data of the last 3 results
- Irregular heartbeat display
- Blood pressure classification - measurements classified using a traffic-light scale
- Certified medical device

TECHNICAL DATA

- Size: approx. 9.26 x 12.95 x 3.03 cm
- Weight: approx. 188 g
- Power supply: batteries 4 x 1.5 V (AAA)
- Measuring range:
 - Blood pressure: 0–299 mmHg
 - Pulse value: 40-199 beats/minute
- Accuracy:
 - Pressure: 5°C–40°C ± 3mm Hg
 - Pulse :± 5% of reading
- Tube length: 60 cm

SCOPE OF DELIVERY

- Upper arm blood pressure monitor
- Cuff (22 – 42 cm)
- Instruction manual
- 4 x 1,5 V batteries (AAA)
- String pouch

LOGISTICAL DATA

Sales packaging
1 piece | 10.5 x 9.8 x 16 cm | 585 g

Packaging unit
4 pieces | 22 x 20.5 x 17.2 cm | 2.5 kg