

Nano-Ionic Facial Steamer DS 600

Art. No. 88248 | EAN 40 15588 88248 7

- Facial steamer with a steam temperature of up to 45°C for deep pore cleansing and hydration of the skin
- Invigorating steam for a natural glow
- Steam development through UV technology and two program settings (15 or 20 min.)
- 10 x more effective than a classic facial steamer due to microfine steam particles that can penetrate deeper into the skin



APPLICATION | FEATURES

- On/off button with one-button operation and white light indicator
- Automatic switch-off time: 15 or 20 min.
- Automatic shut-off when water dries up (red light indicator)
- Recommended to be used with distilled water
- Adjustable spray nozzle with 45-degree precision control
- Maximum liquid capacity: ≥115ml
- First steam development within 1 min. after switching on
- Steam temperature: ≤45°C
- It is recommended to keep a distance of 25 cm to the nozzle
- Exclusive medisana design and compact size

TECHNICAL DATA

- Power: 220-240V
50-60 Hz
320 W
- Cable length: ≥ 1.8 m
- Size: 15.7 × 15.0 × 22.4 cm
- Weight: 0.9 kg

SCOPE OF DELIVERY

- Facial steamer
- Manual

LOGISTICAL DATA

Sales packaging
1 pc | 17.6 x 16.8 x 25.2 cm | 1.3 kg

Packaging unit
4 pcs | 37 x 35.4 x 28.2 cm | 5.8 kg