

Avide LED Ceiling Lamp Oyster Janet 18W 330*60mm NW 4000K

Product code: ACLO33NW-18W-JAN
Brand link:
ID: AB-190518
Company name: Armin Trade Kft.
Company address: Kossuth utca 22 2/4, 4024 Debrecen

QR code:
Date of issue: 2023-09-19
Page: 1/2

SPECIFICATIONS

EAN code: 5999097947143
Warranty: 3year(s)
Material: Plastic+Metal
Working temperature:
Packaging: 1/b 12/c 180/p
Certifications: CE

TECHNICAL DETAILS

Wattage: 18W
Voltage: 220-240V
Beam angle: 120°
Dimmability:
Lumen output: 1 260lm
Color temperature: 4 000K
Lifetime: 15 000h
Type of LED:
CRI: 80
IP standard: IP20

BOX PICTURE



Avide LED Ceiling Lamp Oyster Janet 18W 330*60mm NW 4000K

Product code: ACLO33NW-18W-JAN
Brand link:
ID: AB-190518
Company name: Armin Trade Kft.
Company address: Kossuth utca 22 2/4, 4024 Debrecen

QR code:
Date of issue: 2023-09-19
Page: 2/2

PRODUCT SIZE

Diameter: 330.6mm
 Height: 60mm

CARDBOARD BOX

EAN: 5999097947143
 Packaging: 1/b 12/c 180/p
 Dimensions:
 Net weight: 265g
 Gross weight: 415g

CARTON

EAN: 5999097947150
 Packaging: 1/b 12/c 180/p
 Dimensions:
 Net weight: 3.18kg
 Gross weight: 4.98kg

PALLET EXAMPLE

Height:
 Width: 120cm (std Euro pallet)
 Mepth: 80cm (std Euro pallet)
 Cartons per pallet: 15carton/pallet
 Cartons per row:
 Net weight: 47.7kg
 Gross weight: 74.7kg

PRODUCT PICTURE



PRODUCT OUTLINE

