

**Avide LED Ceiling Lamp Oyster Pandora (ALU) 24W 380\*110mm NW 4000K**

**Product code:** ACLO38NW-24W-ALU  
**Brand link:** [avidelighting.com/qr/ACLO38NW-24W-ALU](https://avidelighting.com/qr/ACLO38NW-24W-ALU)  
**ID:** AB-190518  
**Company name:** Armin Trade Kft.  
**Company address:** Kossuth utca 22 2/4, 4024 Debrecen



**Date of issue:** 2023-09-19

**Page:** 1/2

**SPECIFICATIONS**

**EAN code:** 5999097915845  
**Warranty:** 3year(s)  
**Material:** Aluminium  
**Working temperature:** -20 - +40 °C  
**Packaging:** 1/b 10/c 100/p  
**Certifications:** CE

**TECHNICAL DETAILS**

**Wattage:** 24W  
**Voltage:** 220-240V  
**Beam angle:** 120°  
**Dimmability:** No  
**Lumen output:** 2 100lm  
**Color temperature:** 4 000K  
**Lifetime:** 25 000h  
**Type of LED:** SM2835  
**CRI:** >80  
**IP standard:** IP20

**BOX PICTURE**



**Avide LED Ceiling Lamp Oyster Pandora (ALU) 24W 380\*110mm NW 4000K**

**Product code:** ACLO38NW-24W-ALU  
**Brand link:** [avidelighting.com/qr/ACLO38NW-24W-ALU](https://avidelighting.com/qr/ACLO38NW-24W-ALU)  
**ID:** AB-190518  
**Company name:** Armin Trade Kft.  
**Company address:** Kossuth utca 22 2/4, 4024 Debrecen



**Date of issue:** 2023-09-19  
**Page:** 2/2

**PRODUCT SIZE**

Diameter: 380mm  
 Height: 105mm

**CARDBOARD BOX**

EAN: 5999097915845  
 Packaging: 1/b 10/c 100/p  
 Dimensions: 387mm x 385mm x 110mm  
 Net weight: 572.5g  
 Gross weight: 898g

**CARTON**

EAN: 5999097915852  
 Packaging: 1/b 10/c 100/p  
 Dimensions: 785mm x 395mm x 570mm  
 Net weight: 5.725kg  
 Gross weight: 8.98kg

**PALLET EXAMPLE**

Height:  
 Width: 120cm (std Euro pallet)  
 Mepth: 80cm (std Euro pallet)  
 Cartons per pallet: 10carton/pallet  
 Cartons per row:  
 Net weight: 57.25kg  
 Gross weight: 89.8kg

**PRODUCT PICTURE**



**PRODUCT OUTLINE**

