

Avide LED Strip Blister 12V 22W SMD5050 30LED RGB+2700K IP65 5m WIFI TUYA + IR

Product code: ABLSBL12V5050-30RGBW-TYIR
Brand link:
ID: AB-190518
Company name: Armin Trade Kft.
Company address: Kossuth utca 22 2/4, 4024 Debrecen

QR code:
Date of issue: 2023-09-19
Page: 1/2

SPECIFICATIONS

EAN code: 5999097943664
Warranty: 2year(s)
Working temperature: -20 - +40°C
Packaging: 1/b 20/c 480/p
Certifications: CE

TECHNICAL DETAILS

Wattage: 22W
Voltage: 220-240V
Beam angle: 120°
Dimmability: Yes
Lumen output: 792lm
Color temperature: 2 700K
Lifetime: 25 000h
Energy class: G
Type of LED: SMD5050
LED / meter: 30LED/m
IP standard: IP65

BOX PICTURE



Avide LED Strip Blister 12V 22W SMD5050 30LED RGB+2700K IP65 5m WIFI TUYA + IR

Product code: ABLSBL12V5050-30RGBW-TYIR
Brand link:
ID: AB-190518
Company name: Armin Trade Kft.
Company address: Kossuth utca 22 2/4, 4024 Debrecen

QR code:
Date of issue: 2023-09-19
Page: 2/2

CARDBOARD BOX

EAN: 5999097943664
Packaging: 1/b 20/c 480/p
Dimensions:
Net weight: 415g
Gross weight: 415g

CARTON

EAN: 5999097943671
Packaging: 1/b 20/c 480/p
Dimensions: 395mm x 400mm x 330mm
Net weight: 8.3kg
Gross weight: 8.3kg

PALLET EXAMPLE

Height:
Width: 120cm (std Euro pallet)
Mepth: 80cm (std Euro pallet)
Cartons per pallet: 24carton/pallet
Cartons per row:
Net weight: 199.2kg
Gross weight: 199.2kg

BOX PICTURE

