

REVOLUTION PI

RevPi MIO

Technical Data

Item No.: 100323



Standard	EN 61131-2
Housing dimensions (H x W x D)	96 x 22.5 x 110.5 mm
Housing type	DIN rail housing for TH35 according to DIN EN 60715
Housing material	Polycarbonate
Weight	Approx. 115 g
Protection class	IP20
Power supply	24 V DC (10.8 ... 28.8 V DC)
Maximum power consumption	10 W (system)
Approved operating temperature	-20 ... +55 °C
Approved storage temperature	-40 ... +85 °C
Max. relative humidity (at 40 °C)	93 % (non-condensing)
Interfaces	8 analog inputs 8 analog outputs 4 digital inputs/outputs
Analog Inputs	
Measurement range	0 ... 10 V DC
Input impedance	Voltage >900 kΩ
Max. overall input error	±0.3 % (of full-scale range)
Sample rate	8 ms / 125 Hz
Resolution	1 mV (process image)
Galvanic isolation 24 V supply	Yes ¹ No ²
Analog input modes	Analog input, logic level input
Analog outputs	
Output voltage	0 ... 10 V DC
Max. output current	10 mA 10 V @ 1 K
Sample rate	30 mV peak-to-peak
Max. overall output error	±0.3 % (of full-scale range)

Errors and omissions excepted.
KUNBUS GmbH, Heerweg 15C, 73770 Denkendorf, Germany | Tel: +49 (0) 711 400 91 500 | Fax: +49 (0) 711 400 91 501
Email: info@kunbus.com | Web: https://revolutionpi.com

REVOLUTION PI

RevPi MIO

Data control rate	1 PiBridge cycle
Resolution	4.48 mV
Galvanic isolation 24 V supply	Yes ¹
	No ²
Analog output modes	Analog output, logic level output
Digital inputs/outputs	
Description	Level detection (threshold 1 V) ¹ Type 3 inputs according to EN 61131-2 ² : – Threshold from high to low: 7 V – Threshold from low to high: 10 V – Input current 2.4 mA
GPO [PIN OUT]	$U_{\text{high}} = 22 \text{ V}$ (with $I_{\text{high}} < 20 \text{ mA}$) ¹ U_{high} = positive supply voltage, max. 200 mA ² Short-circuit proof Feedback via GPI [PIN IN] (error message possible)
Digital modes	Digital input, digital output, PWM input, PWM output, pulse input, pulse output, encoder input
EMC interference emission	According to EN 61000-6-4 interference emission for industrial environments ¹
	According to 61000-6-3 interference emission of devices in residential areas ²
EMC immunity	According to EN 61000-6-2 A shielded cable is required for the analog I/Os for cable lengths over 3 m.
Optical display	3 status LEDs (bi-color)
Conformity	CE, RoHS

¹Applies up to product revision 1.1 (indicated on front of housing).

²Applies to product revision 1.2 (indicated on front of housing).