

DSO-200

Mini handheld oscilloscope



Experience precise measurement accuracy and portability like never before with our new DSO-200 handheld oscilloscope. Designed for hobby electronics engineers who value precision and portability, the DSO-200 puts top performance in your hands.

The DSO-200 fits comfortably in your hand and stores easily in your workshop or on your desk, thanks to its foldable stand and compact, rugged design. The ease of use and portability make the DSO-200 your perfect companion.

MAIN FEATURES

Functions	Digital oscilloscope
Stand function	Integrated 90° foldable stand
Battery	1000 mAh lithium battery, rechargeable via USB-C (5 V / 1 A)
Display	2,8" 320x240 LCD Display
Documentation	Included manual in German, English, Spanish, Italian and French

TECHNICAL SPECIFICATIONS

Sampling rate	2,5 MS/s
Bandwidth	200 kHz
Vertical sensitivity	10 mV/Div - 20 V/Div
Horizontal time base	10 µs/Div - 50 s/Div
Test voltage range	X1: 80 Vpp (-40 V - 40 V) X10: 800 Vpp (-400 V - 400 V)
Trigger modes	Auto, normal, single
Coupling	AC, DC
Calibration (Square wave)	Frequency: 1 kHz Duty cycle: 50%

ADDITIONAL INFORMATION

Items shipped	DSO-200, USB-C cable, hand strap, oscilloscope probe, test clip with crocodile clamps, BNC adapter, manual
Dimensions	99 x 69 x 20 mm
Article no.	DSO-200
EAN	4250236826172
Customs tariff no.	90302000