

Support DL 2CA:
CA_1C
CA_1A-3A
CA_1A-26A
CA_1A-20A
CA_1A(P)-38A
CA_1A-7A
CA_1A-8A
CA_1A-28A
CA_1A(P)-40A
CA_1A(P)-41A
CA_1A(P)-42A
CA_3C
CA_3A-26A
CA_3A-7A
CA_3A-20A
CA_3A-28A
CA_3A-32A
CA_3A(P)-38A
CA_3A-8A
CA_3A(P)-40A
CA_3A(P)-41A
CA_3A(P)-42A
CA_7C
CA_7A-8A
CA_7A-20A
CA_7A-28A
CA_8A-32A
CA_8A(P)-38A
CA_8A(P)-40A
CA_8A(P)-41A
CA_20A-32A
CA_20A(P)-42A
CA_20A(P)-38A
CA_28A-32A
CA_28A(P)-40A
CA_38C
CA_40C
CA_41C
CA_42C
Support DL 3CA:
CA_1A-3A-7A
CA_1A-3A-8A
CA_1A-3A-20A
CA_1A-3A-28A
CA_1A-3A-38A

CA_1A-3A-40A
CA_1A-3A-42A
CA_1A-7A-20A
CA_1A-7A-8A
CA_1A-7A-28A
CA_1A-3A-41A
CA_1A-20A-32A
CA_1A-20A-42A
CA_3A-7A-8A
CA_3A-7A-20A
CA_3A-7A-28A
CA_3A-8A-38A
CA_3A-8A-40A
CA_3A-20A-32A
CA_3A-20A-38A
CA_3A-20A-42A
CA_3A-28A-40A
CA_3A-28A-41A
CA_41D
CA_42D
CA_3C-41A
CA_3A-38C
CA_20A-38C
Support UL 2CA:
CA_1A-3A
CA_1A-7A
CA_3A-7A
CA_3A-20A
CA_7A-20A

B38 can't be PCC.

B40 can't be PCC.
B42 can't be PCC.

B41 can't be PCC.

B42 can't be PCC.

B38 can't be PCC.
B40 can't be PCC.

B38 can't be PCC.
B42 can't be PCC.
B40 can't be PCC.
B41 can't be PCC.

B41 can't be PCC.
B38 can't be PCC.
B38 can't be PCC.