



LogiLink®

Solar Extension Cable Set

MC4 male to MC4 female

Art. No.: PHC0100
PHC0101
PHC0102
PHC0103
PHC0104
PHC0105

LogiLink solar extension cables are made of 6 mm² high-quality XLPO wire, with the properties of anti-shock and anti-ultraviolet radiation. They are IP67 waterproof and works in harsh environments. Make sure you can power your home, motorhome, outdoors stably.

Features:

- » Solar extension cable with MC4 male to MC4 female connector
- » Compliant to IEC60332-1-2
- » For connection of the solar panel to the micro inverter (Plus- & Minus-Pol)
- » Wide application for use in outdoor power generation
- » A set with one black and one red solar extension cables



*The specifications and pictures are subject to change without prior notice.
*All trade names referenced are the registered trademarks of their respective owners.

Made in China

Specifications:

Connector 1	MC4 male
Connector 2	MC4 female
Protection Class	IP67
Flame Class	UL94V-0
Cable	Halogen-free, copper, 6 mm ²
Operating Temperature	-40–85°C
Rated Voltage	1000 V DC
Rated Current	30 A
Housing Material	PC, EXL9330
Sealing Ring/Gasket	Silicon rubber
Cable Color	Black/red

Art-No.	Cable Length	EAN Code
PHC0100	1 m	4052792070903
PHC0101	2 m	4052792071917
PHC0102	3 m	4052792070910
PHC0103	5 m	4052792071993
PHC0104	7.5 m	4052792070927
PHC0105	10 m	4052792072006



Package Contents:

- » 1 x Solar Extension Cable, Black
- » 1 x Solar Extension Cable, Red

Package Information:

Art-No.	Packing Dimension	Packing Weight	Carton Dimension	Carton Q'ty	Carton Weight
PHC0100	300 x 200 mm	0.2 kg	mm	pcs	kg
PHC0101	300 x 200 mm	0.45 kg	mm	pcs	kg
PHC0102	300 x 200 mm	0.54 kg	mm	pcs	kg
PHC0103	300 x 240 mm	0.85 kg	mm	pcs	kg
PHC0104	305 x 280 mm	1.24 kg	mm	pcs	kg
PHC0105	305 x 280 mm	1.68 kg	mm	pcs	kg



*The specifications and pictures are subject to change without prior notice.
*All trade names referenced are the registered trademarks of their respective owners.