

YS6MC USB SERIES



Input: 220-240VAC 50/60Hz Output Voltage: 5V DC Rated Power: 6W max

Features

Univeral AC input/ Full range Energy efficiency level VI Leakage Current: < 0.25mA Extremely low leakage current

Protection:Over load/Over voltage/Short circuit

Withstand voltage: 3KV Life Warranty: 3 years

Application

Digital equipment Electric curtains Kitchen appliances Household appliances













Dimensions and Installation








YS6MC USB SERIES

MODEL DETAIL SPEC.		YS6MC-0501200
INPUT	Input Voltage range:	220-240VAC
	Input Frequency:	50/60Hz
	Inrush Current:	65A/ 230VAC
	AC Current:	0.2A/ 230VAC
	Leakage Current:	< 0.25mA/ 240VAC
	Efficiency:	76%
OUTPUT	DC Voltage:	5V
	Rated Current:	1.2A
	Rated Power:	6.0W
	Voltage Tolerance:	±5.0%
	Ripple and Noise:	75mVp-p
	Line Regulation:	±3%
	Load Regulation:	±5%
	Setup, Rise, Hold Up time:	1000ms, 30ms/25ms 230VAC at full load
ENVIRONME NTAL	Operating Temperature:	-20 ~ +60 (Refer to "Derating Curve")
	Storage Temp:	-40℃ ~ 85℃
	Storage Humidity:	10 ~ 95% RH
	Working Humidity:	20 ~ 95% RH non-condensing
PROTECTIO N	Over Load:	Above 110-180% rated output power
		Protection type: Hiccup mode, recovers automatically after fault condition is removed
	Over Voltage:	>120% rated output power
		Protection type: Shut down o/p voltage, re-power on to recover
	Short Circuit :	Shut down o/p voltage, re-power on to recover
SAFETY & EMC	Safety Regulations:	EN62368-1
	Withstand Voltage:	I/P-O/P:3KVAC I/P-FG:2KVAC O/P-FG:0.5KVAC
	Isolation Resistance:	I/P-O/P, I/P-FG, O/P-FG:100M Ohms / 500VDC / 25°C/ 70% RH
	EMC Emission:	Compliance to EN55032 (CISPR32), Class B, EN61000-3-2,-3,
	EMC Immunity:	EN61000-4-2,3,4,5,6,8,11
OTHER	MTBF:	100Khrs min. MIL-HDBK-217F(25℃)
	Size:	67*37*20mm
	Weight:	27g / pcs
	Packaging:	200PCS/CTN



YS6MC USB SERIES

Deduction curve and temperature



Minus output and input voltage curves

