

LogiLink®

USB 3.2 Gen 1 Active Repeater Cable Amplifier

Art. No.: UA0177
UA0400
UA0401


The USB 3.2 Gen 1 Active Repeater Cable enables you to extend an USB connection for longer distance by daisy-chain. Built in amplifier for stable signal transmission even with long distance. Additional DC jack is designed for devices which need more power, such as USB hard drive.

Features:

» Comply with USB 3.2 Gen 1 specifications, transfer speeds up to 5 Gbps
» With amplifier for stable signal transmission
» Built-in port-status LED indicator
» Supports 8 kV (air) ESD surge protection
» USB bus power/DC self-power
» Support daisy-chain connection
» Over current detection and protection
» Plug & Play, no driver required
» Supports Windows, Mac OS and Linux



Art-No.	Cable Length	EAN Code
UA0177	10 m	4052792012835
UA0400	20 m	4052792069273
UA0401	30 m	4052792069280





Daisy-Chain connection available, you can connect multiple repeater cables to extend USB connection.

*The specifications and pictures are subject to change without prior notice.
*All trade names referenced are the registered trademarks of their respective owners.

Specification:

Art. No.	UA0177	UA0400	UA0401
Cable Length	10 m	20 m	30 m
USB Standard	USB 3.2 Gen 1		
Max. Data Transfer Rate	Up to 5 Gbps		
Input	USB 3.0-A male & DC 2.35 mm jack (power)		
Output	USB 3.0-A female		
Max. Daisy Chain Distance	50 m	40 m	40 m
Hot Swap and Plug & Play	Yes		
Safety Protection	Over current 5 V/2 A protection		
ESD Surge Protection	8 kV (air) ESD surge protection		
Max. Power Consumption	0.23 W	0.7 W	1.2 W
LED Indicator	LED for power and activity		
Operating Temperature	0–50°C		
Operating Humidity	0–85% RH (no condensation)		
Optional Power Supply If Needed	External Power Supply 5 V/2 A		
Compatibility	Windows, Mac OS, Chrome OS and Linux		
Weight	0.75 kg	1.5 kg	2.2 kg
Color	Black cable, blue case		

Package Contents:

» 1x USB Active Repeater Cable
» 1x User Manual

Package Information:

Art-No.	Packing Dimension	Packing Weight	Carton Dimension	Carton Q'ty	Carton Weight
UA0177	226 x 140 x 116 mm	0.94 kg	600 x 250 x 300 mm	10 pcs	9.4 kg
UA0400	235 x 202 x 122 mm	1.8 kg	424 x 251 x 358 mm	5 pcs	9.7 kg
UA0401	235 x 202 x 122 mm	2.6 kg	424 x 251 x 358 mm	5 pcs	13.7 kg

*The specifications and pictures are subject to change without prior notice.
*All trade names referenced are the registered trademarks of their respective owners.