

## VOLTCRAFT – TOP PERFORMANCE IN EVERY WAY

For more than 40 years, our product range has been dynamically adapting to the constant changes in the industry. We commit to offering first-class quality to our customers while delivering an excellent cost-performance ratio. This philosophy remains the cornerstone of Voltcraft's success.

## IST3003 EVSE ADAPTER



Item no. 2997217

Test adapter for charging station (Wallbox).

### FEATURES

Enabling testing of EV charge points // Compatible with any VDE0100 tester // Smallest size

### TECHNICAL DATA

Input voltage	max. 250 V (single phase), max. 430 V (three phase) 50/60 Hz
Measurement Category	CAT II 300 V
Mains socket rating	250 V/10 A
Mains socket protection Fuse	T10 A/250 V
PP simulation Open circuit	13 A, 20 A, 32 A, 63 A
CP simulation States	A, B, C, D
Error simulation	CP error "E", PE (earth fault) error
PE Pre-Test	Yes
Test connector type	IEC62196-2 Type 2 male
Test cable length	6.1 cm (2.4"), 240 x 320 pixels
Standards	EN61010-1
IP Rating	IP 40
Height	2000 m
Pollution degree	2
Operation temperature	0 to +40 °C / < 80 % rH (non-condensing)
Storage conditions	-10 °C to +50 °C / < 80 % rH (non-condensing)
Product size (W x H x D)	174 x 105 x 72 mm
Weight	0.83 kg



## **EQUIPMENT**

PP simulation (open circuit) 13 A, 20 A, 32 A, 63 A // CP simulation states: A, B, C, D // Standards: EN61010-1 // IP Rating IP 40 // Pollution degree 2

## **PACKAGE CONTENTS**

EVSE adapter // Carrying bag // Manual