



PRODUCT

Integrity 12 Inch Vinyl Gloves

600-0640

Integrity 12" Vinyl gloves, ISO 6 powder-free, bulk packed in packs of 100, cleanroom packaged and double bagged. ESD safe therefore suitable for protection for operators and processes in the microelectronics and semiconductor industries, in addition to pharmaceutical, aerospace, automotive and medical. Ambidextrous bulk packed, 5 years shelf life from date of manufacture.

PRODUCT CODE	PACK QTY	SIZE
600-0640	100 gloves	Small
600-0641	100 gloves	Medium
600-0642	100 gloves	Large
600-0643	100 gloves	X-Large

MEASUREMENT	TEST METHOD	RESULT
		Vinyl glove
Surface resistance ohms	JIS K6911	$10^7 \times 10^9$ ohms

To request a quotation or for more information, please call **+44 (0)1473 836205** email info@integritycleanroom.com or visit www.integritycleanroom.co.uk

IMPORTANT: This data sheet and its contents (the "Information") belong to Integrity Cleanroom or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but Integrity Cleanroom assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where Integrity Cleanroom was aware of the possibility of such loss or damage arising) is excluded. © Integrity Cleanroom.

SIZE	SMALL	MEDIUM	LARGE	X-LARGE	TEST CODE
Width of palm (mm)	88±2	98±2	108±2	113±2	ASTM D5250
Total length (m/m) from tip middle finger to cuff	Min. 300	Min. 300	Min. 300	Min. 300	
Length of fingers (mm)					± 1.0
Thumb	56	61	62	67	
Index finger	64	72	77	85	
Middle finger	73	83	91	97	
Ring finger	69	77	83	89	±1.0
Little finger	53	59	62	66	
Circumference of fingers (mm)					±1.0
Thumb	66	74	82	82	
Index finger	58	62	70	71	
Middle finger	56	60	70	71	
Ring finger	54	60	70	70	
Little finger	50	56	63	63	
Before and after accelerated aging (70± 2°C x 72 ± 2h) tensile strength (mpa)	Min. 9 mpa	Min. 9 mpa	Min. 9 mpa	Min. 9 mpa	ASTM D5250 Min. 9 mpa
Before and after accelerated aging elongation (%)	Min. 350%	Min. 350%	Min. 350%	Min. 350%	ASTM D5250 Min 300%
Thickness (mm)					
Finger tip	Min. 0.08	Min. 0.08	Min. 0.08	Min . 0.08	ASTM D5250 Min 0.05
Palm	Min. 0.08	Min. 0.08	Min. 0.08	Min. 0.08	ASTM D5250 Min. 0.08
Cuff	Min. 0.06	Min. 0.06	Min. 0.06	Min. 0.06	

To request a quotation or for more information, please call **+44 (0)1473 836205**
 email info@integritycleanroom.com or visit www.integritycleanroom.co.uk

IMPORTANT: This data sheet and its contents (the "Information") belong to Integrity Cleanroom or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but Integrity Cleanroom assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where Integrity Cleanroom was aware of the possibility of such loss or damage arising) is excluded. © Integrity Cleanroom.