



- easy handling
- straight action principle
- ratchet release
- contact positioning with flap locator type FC
- precisely ground profiles
- burnished surface
- ergonomically formed soft grips
- colour: rape yellow/signal black
- fully recyclable; RoHS complied
- application range: FC1 contacts
- wire gauge: profile 1: 0,09-0,20mm²
- profile 2: 0,20-0,50mm²
- weight approx. 610 g

for FC1 crimp contacts:					
09 06 000 9574	male	2	0,09-0,25	28-24	0,7-1,5
09 06 000 9554	male	1	0,09-0,25	28-24	0,7-1,5
09 06 000 8484	female	2	0,09-0,25	28-24	0,7-1,5
09 06 000 8474	female	1	0,09-0,25	28-24	0,7-1,5
09 06 000 6464	female	Sn	0,09-0,25	28-24	0,7-1,5
contact no.	male / female	PL	wire gauge	AWG	InsulationØ

	All rights reserved Department EL PD	All Dimensions in mm Original Size DIN A3		Scale 1:1	Free size tol.	Ref.
		Created by WAERMKER	Inspected by HAERTLING	Standardisation HOFFMANN	Date 2020-05-07	State Final Release
HARTING Electronics GmbH D-32339 Espelkamp		Title Crimpset FC1			Doc-Key / ECM-Nr. 100888471/UGD/000/A 500000172513	
		Type TB	Number 09990000771		Rev. A	Page 1/1