Pushing Performance
Since 1945

D-Sub Hood 9 poles top entry metal 100

Part number	09 67 009 0344 280
Specification	D-Sub Hood 9 poles top entry metal 100
HARTING eCatalogue	https://b2b.harting.com/09670090344280

Identification

Category	Hoods/Housings
Series of hoods/housings	D-Sub
Type of hood/housing	Shell housing
Description of hood/housing	Cover can be screwed on

Version

Size	D-Sub 1
Version	Top entry
Cable entry	1x
Cable fixing	Cable clamp Tension relief ≤ 6.5 mm
Locking type	With short locking screws Thread 4-40 UNC
2 parts	Yes
Separable	Yes

Technical characteristics

Tightening torque	0.4 Nm Locking screw 0.4 Nm cover screw 0.4 Nm Cable clamp screw
Ambient temperature	-35 ... +100 °C
Cable diameter	3 ... 9.5 mm

Material properties

Material (hood/housing)	Metal
Length	39.5 mm

HARTING Electronics GmbH | Marienwerderstraße 3 | 32339 Espelkamp | Germany
Phone +49 5772 47-97200 | electronics@HARTING.com | www.HARTING.com

Pushing Performance
Since 1945

Material properties

Width	31.8 mm
Height	15.4 mm

Specifications and approvals

UL / CSA	UL 1977 ECBT2.E102079

Commercial data

Packaging size	100
Net weight	47.3 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140221475
eCl@ss	27440213 D-Sub hood

HARTING Electronics GmbH | Marienwerderstraße 3 | 32339 Espelkamp | Germany
Phone +49 5772 47-97200 | electronics@HARTING.com | www.HARTING.com