

Han3A RJ45 PFT HIFF adapter



Image is for illustration purposes only. Please refer to product description.

Part number	09 45 515 0024
Specification	Han3A RJ45 PFT HIFF adapter
HARTING eCatalogue	https://b2b.harting.com/09455150024

Identification

Category	Connectors
Series	RJ45
Element	Adapter
Specification	To mount HIFF inserts

Version

Size	Han [®] 3 A
Shielding	Unshielded

Technical characteristics

Limiting temperature	-40 ... +70 °C
Mating cycles	≥500

Material properties

Material (hood/housing)	Polycarbonate (PC)
Colour (hood/housing)	Black
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained



Pushing Performance
Since 1945

Material properties

California Proposition 65 substances	Yes
--------------------------------------	-----

California Proposition 65 substances	Nickel
--------------------------------------	--------

Specifications and approvals

Approvals	DNV GL
-----------	--------

Commercial data

Packaging size	1
----------------	---

Net weight	3.3 g
------------	-------

Country of origin	Romania
-------------------	---------

European customs tariff number	85366990
--------------------------------	----------

GTIN	5713140060944
------	---------------

eCl@ss	27440292 Connector component (accessories)
--------	--