



In set inclusive:

Number	Description
2	Crimp flange 6,0-7,0
2	Crimp ferrule 9,5-10,5
1	Blanking piece 9-37
1	Label Line A, B, A+B

	All rights reserved		Scale 1:1	Free size tol.		Ref.												
	Department EL PD		Created by ZENG D	Inspected by LUOK	Standardisation ROEBEN	Sub.												
			Title InduCom 9 male CAN 4-40 UNC			Date 2021-07-16												
D-32339 Espelkamp			Type TB	Number 66630095113		State Final Release												
<table border="1"> <tr> <td>6663 009 5113 170</td> <td>PL1</td> <td>Plated hood</td> </tr> <tr> <td>6663 009 5113 777</td> <td>PL1</td> <td>Small batch</td> </tr> <tr> <td>6663 009 5113</td> <td>PL1</td> <td>Standard batch</td> </tr> <tr> <td>Part number</td> <td>Performance level</td> <td>Remark</td> </tr> </table>			6663 009 5113 170	PL1	Plated hood	6663 009 5113 777	PL1	Small batch	6663 009 5113	PL1	Standard batch	Part number	Performance level	Remark	Doc-Key / ECM-Nr. 100869636/UGD/001/C 500000198818			Rev. C
6663 009 5113 170	PL1	Plated hood																
6663 009 5113 777	PL1	Small batch																
6663 009 5113	PL1	Standard batch																
Part number	Performance level	Remark																
			Page 1/1															