




Pushing Performance  
Since 1945

## Han-Fast Lock 10mm<sup>2</sup> m.Pin Ag Ro 2300St.



Part number	09 08 000 6124
Specification	Han-Fast Lock 10mm <sup>2</sup> m.Pin Ag Ro 2300St.
HARTING eCatalogue	<a href="https://b2b.harting.com/09080006124">https://b2b.harting.com/09080006124</a>

### Identification

Category	Contacts
Series	Han-Fast <sup>®</sup> Lock
Type of contact	PCB contact
Description of the contact	With pin

### Version

Pack contents	2300 pieces on reel
---------------	---------------------

### Technical characteristics

Conductor cross-section	10 mm <sup>2</sup>
Operating current	≤60 A
Contact resistance	≤2 mΩ
Stripping length	7.5 mm

### Material properties

Material (contacts)	Copper alloy
Surface (contacts)	Silver plated
Material (locking)	Copper alloy
Surface (locking)	Passivated
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained



Pushing Performance  
Since 1945

## Material properties

REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead
ECHA SCIP number	b51e5b97-eeb5-438b-8538-f1771d43c17d
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel

## Specifications and approvals

UL / CSA	UL 1977 ECBT2.E235076 CSA-C22.2 No. 182.3 ECBT8.E235076
----------	--

## Commercial data

Packaging size	1
Net weight	9,080 g
Country of origin	Germany
European customs tariff number	85366990
GTIN	5713140014831
eCl@ss	27460201 PCB connector (board connector)