




Connector Location A

Connector Location B



C	23	09457151383		100
	22	09457151382		90
	21	09457151381		80
	20	09457151380		70
	19	09457151379		60
	18	09457151378		50
	17	09457151377		40
	16	09457151376		30
D	15	09457151385		25
	14	09457151375		20
	13	09457151374		15
	12	09457151373		10
	11	09457151372		9
	10	09457151371		8
	9	09457151370		7
E	8	09457151369		6
	7	09457151368		5
	6	09457151367		4
	5	09457151366		3
	4	09457151365		2
	3	09457151364		1.5
	2	09457151363		1
	1	09457151362		0.5
F	Cont. no.	Part no.	Type of cable	Dim. a[m]

RJ45 Ethernet Hybrid Cable, 4xAWG 22/7 + 4x1.5sqmm (shielded), FRNC, Cat. 5, green



Protection level: IP65/67
Temperature range: -20°C ... +70°C

	All rights reserved	Created by BANIUD Banciu	Inspected by 402676 Gross	Standardisation MUNTEANV Muntean	Date 2021-07-08	State Final Release
	Department HCS - RO	Title Han 3A RJ45 Hybrid Cable Assembly		Doc-Key / ECM-Nr. 100173949/UGD/003/E 500000198811		
HARTING Customised Solutions D-32339 Espelkamp		Type TB	Number 094571513XX		Rev. E	Page 1/1