

Highlights

- **3 speed levels**
low, medium, high
- **Internal swivelling function**
The swivelling function distributes the cooled air optimally to all areas of the room.
- **Air purifier**
The sucked-in air is washed through the filter. Dust, pollen, mites, bacteria and unpleasant odours are filtered out of the air.
- **Anion**
Ionisers in air purifiers generate negatively charged ions (anions), which combine with positively charged dirt particles in the room air to form larger clusters
- **45 litre water tank**
Operation up to 15 hours possible.



This powerful air cooler is the key to your cooling oasis. With an impressive 115 watts of power, it offers lightning-fast cooling that you can feel.

No more constant topping up of water!

With a generous 45-litre water tank, you can enjoy the pleasant coolness for hours without having to worry about the hassle of refilling.

Whether it's an entrance hall, large office or business premises - the air cooler is designed for rooms with an effective area of 35 square metres and provides extensive coverage.

The swivelling function ensures that the refreshing air flow reaches every corner of your room. So you can feel comfortable anywhere in the room.

With an impressive air circulation of 3200 cubic metres per hour, you'll experience the fast and efficient cooling you need on the hottest days.

Washable dust and water filters and an integrated ioniser ensure thorough cleaning of the air and neutralise unpleasant odours. The air drawn in is cleaned by the filters, effectively removing dust, pollen, mites, bacteria and unpleasant odours from the air.

Use the timer function, the user-friendly touch control panel or the practical remote control to control the air cooler as you wish. It adapts to your needs.

Note: Due to the high humidification performance of the device, a sufficient supply of air is required indoors. The device is particularly suitable for use in workshops, well-ventilated rooms and outdoors.



Scope of delivery

- Air cooler
- Remote control
- Operating instructions

Warranty period

- 2 years



Front view



Oblique view left



Oblique view right



Side view

Specifications:

- 3 in 1: cooling, humidification, ventilation
- Air circulation 3200 m³/h
- Effective area 35 m²
- Power consumption: 115 watts
- Water tank capacity 45 litres
- Operating time with full tank 9 - 15 hours
- Water evaporation 3 to 5 litres per hour
- 3 levels
- Air purifier with ioniser (anion)
- Special rotor blade
- Castors
- Easy to fill water tank
- Touch control panel

Dimensions:

- Product (W×H×D): 490×1080×390 mm
- Packaging (W×H×D): 540×1100×430 mm
- Net/gross weight: 15 kg / 16.5 kg

