

Hikvision HWD-5108MH(S) Digitaler Videorekorder (DVR) Schwarz

Marke : Hikvision

Artikel-Code: HWD-5108MH(S)



Produktname : HWD-5108MH(S)

Hikvision HWD-5108MH(S). Produktfarbe: Schwarz, Maximale Video-Auflösung: 1920 x 1080 Pixel, Videokompressionsformate: H.264, H.264+, H.265, H.265 Pro, H.265 Pro+. Video-Eingangskanäle: 8 Kanäle. Ethernet Schnittstellen Typ: Schnelles Ethernet, Unterstützte Netzwerkprotokolle: TCP/IP, PPPoE, DHCP, Hik-Connect, DNS, DDNS, NTP, SADP, SMTP, NFS, iSCSI, UPnP, HTTPS. Maximaler HDD Speicher: 4 TB. DC-Spannung: 12 V, Stromverbrauch (Standardbetrieb): 17 W

Leistungen		Netzwerk	
Maximale Video-Auflösung	1920 x 1080 Pixel	Ethernet/LAN	✓
Videokompressionsformate	H.264, H.264+, H.265, H.265 Pro, H.265 Pro+	Ethernet Schnittstellen Typ	Schnelles Ethernet
Unterstützte Audioformate	G.711 µ-law	Unterstützte Netzwerkprotokolle	TCP/IP, PPPoE, DHCP, Hik-Connect, DNS, DDNS, NTP, SADP, SMTP, NFS, iSCSI, UPnP, HTTPS
Eingebaut	✗		
Video-Capture Geschwindigkeit	30 fps		
Anzahl Kanäle	8 Kanäle		
Produktfarbe *	Schwarz		
Audio input Kanäle	1 Kanäle		
Audio Kanäle	1.0 Kanäle		
Maximale Framerate	30 fps		
USB Anschluss	✓		
Videostreaming	✓		
Dual-Stream-Unterstützung	✓		
Bitrate	64 Kbit/s		
Anzahl der gleichzeitig abgespielten Kanäle	8 Kanäle		
Anschlüsse und Schnittstellen		Festplatte	
Video-Eingangskanäle	8 Kanäle	Maximaler HDD Speicher	4 TB
Anzahl USB 2.0 Anschlüsse	2		
		Energie	
		DC-Spannung	12 V
		Stromverbrauch (Standardbetrieb)	17 W
		Gewicht und Abmessungen	
		Breite	260 mm
		Tiefe	222 mm
		Höhe	45 mm
		Gewicht	1 kg
		Betriebsbedingungen	
		Betriebstemperatur	-10 - 55 °C
		Relative Luftfeuchtigkeit in Betrieb	10 - 90%

Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.