

## Product Datasheet

**Product code:** **34A.SA.1**

**Product type:** High precision tweezers

**Made in:** Switzerland


**Description:** Type 34A high precision tweezers are suitable to applications which require holding a flat component firmly. The line serration provides the handles with extra grip.

**Tip description:** straight, thin, squared, flat, superior finish

**Coating/finishing:** Sandblasted

**Body material:** Anti-Magnetic Anti-Acid Stainless Steel (SA)



**Picture:**



**Tweezer dimensions:**

OAL	120.0 mm – 4.724 inch
Width	10.0 mm – 0.394 inch
Height	11.0 mm – 0.433 inch

**Tip details:**



**Tip dimensions:**

Tip width	6.30 mm – 0.248 inch
Tip thickness	0.17 mm – 0.007 inch