

Revolutionary wireless mobile battery scanner

Whatever the place, wherever you are : IRIScan Anywhere 6 Wifi is a light, autonomous, standalone, high resolution, lithium battery powered portable colour document scanner that allows you to scan contracts, shipping notes, invoices , receipts , medical prescription, patient files records, business cards, pages , letter & A4 color documents.

IRIScan Anywhere 6 Wifi can easily be transported & connected wireless to your smartphone or tablet on the go. It's an ideal companion for those on the go who needs to scan important documents with always a very high quality image standard whatever the paper size (up to A4/letter), the paper type (glossy, matte, plastic - ID card, credit card, medical card, etc.) and whatever the environment you are in (outside, inside, sunny, dark, over exposed , etc.). All images will be stored in your smartphone' preferred directory thanks to the free App "IRIScan PDF scanner" ready to be shared immediately to your office, colleague or secretary.

Business men dealing with legal & invoice management, medical prescription, patient file management, hospital & service desk, ID Cards or business card management, shipping notes or banking & finance document workflow will be delighted to capture perfect quality image' documents on the go or via USB cable when at office.

Powered by HQ OCR , IRIS highest Quality Optical Character Recognition, you will be able to convert scanned images into searchable PDFs, editable Word, Excel or Text while supporting up to 138 languages.

Such new companion helps you empowering the enterprise' productivity while increasing big time employee' satisfaction.

Key Features

- Scan anywhere with a smartphone, tablet or PC.
- Fast scanning speeds at up to 4 seconds per page (15 ppm) in USB mode.
- One side document (simplex scan).
- Scan directly to JPEG/TIFF/PDF and other image format.
- Choose scan file prefix & time format.
- Rechargeable Lithium battery power scan up to 180 pages between battery charges.
- Scanning resolutions: 300/600 dpi (1200 interpolated).
- Free IRIScan PDF scanner App to share your scans to ANY tablet or smartphone device (iOS®/Android™).
- Get editable document with free Readiris™ OCR software included.
- Enjoy professional PDF management with a free 30 days trial Readiris™ PDF for PDF creation, annotations, comments or signature.
- Convert to Word, Excel, PDF, etc.

Quick Reference Guide

Product name	IRIScan™ Anywhere 6 Wifi
SKU	461855
EAN code	5420079900950
UPC-A code	765010766437
Mercury code	(91)3877V398
Box size (L x D x H)	355 x 166 x 68 mm - 13.98 x 6.54 x 2.68 in
Box weight	840 g (1.85 lbs)
Box languages	English, French, German, Dutch, Italian, Spanish, Portuguese, Arabian, Simplified Chinese, Hebrew
Box content	Scanner • Calibration card • USB-C cable • Getting started guide

Scanner specifications

Scanning speed & Format	4sec – Up to 15PPM – A8-A4 / Letter size 8.5 x 11 in
Type of Scanner & Light Source	Single sheet – CIS – Simplex – RGB LED
Scanner dimension	294 x 52 x 47 mm - 11.57 x 2.047 x 1.85 in
Color Depth & Resolution	24 bit – 300/600 dpi & 1200 dpi interpolated
Composite of Battery & Battery weight	Lithium-ion cell & 48gr – 0.11lbs
Number of lithium cells / lithium content in grams	1 & 0.825 g
Power	USB powered USB-C
Power Consumption Scanning operating	4.5 W
Power Consumption Ready & OFF	1.6 W & 0.1 W
Maximum DAILY DUTY CYCLE in pages per day	500 pages
Battery life operating (Number of scans)	260 scans WIFI ON
Scanner Life	20,000 scans
Scanner Weight in kg & lbs	480g & 1.058 lbs
Compatibility	Twain/WIA/ICA
Scanning Width in inch/cm	8.5inch/21.6cm
USB Port	USB-C
Charging Time in hours	4.5hrs
Wireless LAN Specification parameters	802.11 a/b/g/n/ac
Acoustical Noise in operation	≤ 55 dB

Minimum computer requirements

Scanner

- At least one USB port available
- Wifi connection available
- Compatible with latest Android® and iOS® versions

Software suite for Windows® and macOS®

- Intel® based PC or equivalent recommended
- Microsoft® Windows® 11, 10
- Mac® computer with Intel 64® Arm processor
- macOS® X version 12.x or above
- 512MB RAM recommended
- 1GB of available hard disk space
- Internet connection for software download



IRIScan-PDF Scanner



www.irislink.com

I.R.I.S. s.a. - 10 rue du Bosquet - 1348 Louvain-La-Neuve - Belgium

marketing.distri@iriscompany.com

I.R.I.S. Inc. - 55 NW 17th Avenue, Unit D - Delray Beach, Florida 33445 United States

Canon
CANON GROUP

THL231018-447

© Copyright 2023 I.R.I.S. s.a.
All rights reserved for all countries. IRIS, IRIS' product names, IRIS' logos and IRIS' product logos are IRIS trademarks. All other products and names mentioned are trademarks or registered trademarks from their respective owners.

