

## Hook-and-Loop Cable-Tie Set Item-No.: 23CA184 ... 23CA189 10m-Roll Item-No.: 23CA190/191



These hook-and-loop cable-ties made of polyamide are easy to open and close again. Therefore, they are ideally suited for general bundling tasks and fixations of, for example, objects, cables, sports utensils, plants, curtains, tools and much more. The excellent material properties of polyamide allow a wide range of applications as far as environmental conditions are concerned. The material is dimensionally stable, robust and resistant to many liquids and also UV radiation. The supply set of 10 hook-and-loop cable ties with eyelet content is optimal for any indoor and outdoor applications. The black design can be unrestricted and inconspicuous in many usages.



**Technical data:** Material: Polyamide • Temperature range: -20 ... 85 °C • Melting temperature: >250 °C • Color: black • RoHS compliant, REACH compliant.

Part-No.	Description	Length	Width	Color	Content	EAN / GTIN
23CA184	Hook-and-loop cable-ties 150 x 12 mm Set (Black)	150 mm	12 mm	Black	10 pcs.	4260732283935
23CA185	Hook-and-loop cable-ties 200 x 12 mm Set (Black)	200 mm	12 mm	Black	10 pcs.	4260732283942
23CA186	Hook-and-loop cable-ties 250 x 12 mm Set (Black)	250 mm	12 mm	Black	10 pcs.	4260732283959
23CA187	Hook-and-loop cable-ties 300 x 14 mm Set (Black)	300 mm	14 mm	Black	10 pcs.	4260732283966
23CA188	Hook-and-loop cable-ties 350 x 14 mm Set (Black)	350 mm	14 mm	Black	10 pcs.	4260732283973
23CA189	Hook-and-loop cable-ties 400 x 16 mm Set (Black)	400 mm	16 mm	Black	10 pcs.	4260732283980



Part-No.: 23CA190 – Hook-tape including 50 buckles for flexible use and cutting

Part-No.: 23CA191 – Hook-and-loop-tape without buckles for flexible use and cutting

**Technical data:** Material: Polyamide • Temperature range: -20 ... 85 °C • Melting temperature: >250 °C • Color: black • RoHS compliant, REACH compliant.

Part-No.	Description	Length	Width	Color	Content	EAN / GTIN
23CA190	Hook-tape 10 m x 20 mm Roll w/ bucklets	10 m	20 mm	Black	10 m	4260732283997
23CA191	Hook-and-loop tape 10 m x 20 mm Roll	10 m	20 mm	Black	10 m	4260732284130