

Polyester Braided Sleeving (bulk stock)

No.: 23CA192...202



This cable braided sleeve is the optimal and cost-effective solution when it comes to protecting and bringing together cables and wires. This flexible cable sleeving can also be used as an abrasive protection and as an inhibitor of animal bites. The tightly woven braid hugs the contents and keeps them together, protected and clean. The material is weather resistant, durable and looks good doing it! The application is very simple and can be customized by shortening to the desired length. The cut can be made using the hot cutting method or by means of scissors / string cutter and subsequent heat sealing of the open ends. It is possible to lead out individual cables on the track through the slot.

To prevent fraying, the sleeve should be cut with a hot cutting tool!

Technical data: Material: polyester braid • Temperature range: -55 ... 155 °C • Melting temperature: 230 °C • Color: black • Tensile strength max. 10.4 MPa • RoHS compliant, REACH compliant, halogen free • Flammability class based on UL94HB.

Part-No.	Description	Bundle Ø	Bundle Ø max.	Selling unit	Complete reel	
					Content / max. length	EAN/GTIN
23CA192	Braided Sleeving 5 mm Black, PES (100m)	5 mm	6 mm	1 m +	100 m	4260732284161
23CA193	Braided Sleeving 8 mm Black, PES (100m)	8 mm	9 mm	1 m +	100 m	4260732284178
23CA194	Braided Sleeving 10 mm Black, PES (100m)	10 mm	11 mm	1 m +	100 m	4260732284185
23CA195	Braided Sleeving 13 mm Black, PES (100m)	13 mm	14 mm	1 m +	100 m	4260732284192
23CA196	Braided Sleeving 16 mm Black, PES (100m)	16 mm	17 mm	1 m +	100 m	4260732284208
23CA197	Braided Sleeving 19 mm Black, PES (50m)	19 mm	20 mm	1 m +	50 m	4260732284215
23CA198	Braided Sleeving 25 mm Black, PES (50m)	25 mm	26 mm	1 m +	50 m	4260732284222
23CA199	Braided Sleeving 29 mm Black, PES (50m)	29 mm	30 mm	1 m +	50 m	4260732284239
23CA200	Braided Sleeving 32 mm Black, PES (50m)	32 mm	33 mm	1 m +	50 m	4260732284246
23CA201	Braided Sleeving 38 mm Black, PES (25m)	38 mm	39 mm	1 m +	25 m	4260732284253
23CA202	Braided Sleeving 50 mm Black, PES (25m)	50 mm	51 mm	1 m +	25 m	4260732284260