

Soft-Grip-Texture-Shrinking-Tubes 1 m

Item-No.: 23CA217 ... 23CA227



This shrinking tube with textured “Soft-Grip” surface is ideally suited to increase or restore the grip of handles. Furthermore, the pattern gives a great look. Perfect for tennis rackets, fishing rods, tools, bicycles, pool cues, field hockey sticks or any other application! The product is designed to last and that is why it is made of high purity polyolefin. Optimal results can be achieved by a shrinking process with a heat gun or similar - open flames are not suitable for this purpose!

Technical Specifications

Shrink ratio: 2:1 • Shrinking temp.: 90 ... 120 °C • Temperature range: -50 ... 120 °C • Material: Polyolefin • Tensile strength: > 10.4 MPa • Color: Black (textured) • Dielectric Strength: 15 kV/mm (30 s.) • Length: 1 m.

Versions

Part-No.	Description	Inner Ø before shrink (appx.)	Inner Ø after shrink (appx.)	Content	EAN / GTIN
23CA217	Soft-Grip-Texture-Shrinking-Tube 1m Ø 15 mm Black	15 mm	8 mm	1 m	4260732284413
23CA218	Soft-Grip-Texture-Shrinking-Tube 1m Ø 18 mm Black	18 mm	9 mm	1 m	4260732284420
23CA219	Soft-Grip-Texture-Shrinking-Tube 1m Ø 20 mm Black	20 mm	10 mm	1 m	4260732284437
23CA220	Soft-Grip-Texture-Shrinking-Tube 1m Ø 22 mm Black	22 mm	11 mm	1 m	4260732284444
23CA221	Soft-Grip-Texture-Shrinking-Tube 1m Ø 25 mm Black	25 mm	13 mm	1 m	4260732284451
23CA222	Soft-Grip-Texture-Shrinking-Tube 1m Ø 28 mm Black	28 mm	14 mm	1 m	4260732284468
23CA223	Soft-Grip-Texture-Shrinking-Tube 1m Ø 30 mm Black	30 mm	15 mm	1 m	4260732284475
23CA224	Soft-Grip-Texture-Shrinking-Tube 1m Ø 35 mm Black	35 mm	18 mm	1 m	4260732284482
23CA225	Soft-Grip-Texture-Shrinking-Tube 1m Ø 40 mm Black	40 mm	20 mm	1 m	4260732284499
23CA226	Soft-Grip-Texture-Shrinking-Tube 1m Ø 45 mm Black	45 mm	23 mm	1 m	4260732284505
23CA227	Soft-Grip-Texture-Shrinking-Tube 1m Ø 50 mm Black	50 mm	25 mm	1 m	4260732284512

Please shrink with a heat gun or similar - open flames are not suitable for this purpose! Products are not for children!