

Miniature Bulb Lamp E10 Transparent

Part-No.: 22O183, 23O184 ... 23O188



Socket: E10



Dimensions in mm

This universal small bulb lamp (E10 socket) is ideal for hobbyists, DIY enthusiasts, model makers and workshops. The classic style of the bulbs opens a wide range of use for various applications: Indication, general lighting, model making, model railroads or crib lighting. Also, many old bicycle lamps or lighting can be repaired with it.

Technical data: Traditional glow-wire bulb · E10 globe lamp clear, on E10 socket · Dimensions: 11 x 23 mm.

Part-No.	Operating voltage	Current consumption appx.	Power consumption @ operating voltage	EAN/GTIN (Packing-Unit 50x)
22O183	4.8 V	0.50 A	2.4 W	4260732282921
23O184	1.5 V	0.30 A	0.45 W	4260732284000
23O185	2.5 V	0.30 A	0.75 W	4260732284017
23O186	3.8 V	0.30 A	1.14 W	4260732284024
23O187	6.0 V	0.50 A	3 W	4260732284031
23O188	12 V	0.25 A	3 W	4260732284048

Attention: the product is sensitive to mechanical shocks. Lifetime approx. 1000 h (depending on environmental conditions). Please note the maximum value of the voltage supply. Polarity is not required.

Accessories:

Lamp-Stand-Socket E10, Diameter: 9.8 mm · Height: 13 mm · Pin length (total): 19 mm · Hole distance: 15 mm.



Part-No.	Description	EAN/GTIN
23O189	E10 Lamp-Stand-Socket, Copper (yellow)	4260732284055
23O190	E10 Lamp-Stand-Socket, Copper & Nickel plated (silver)	4260732284062