

TECHNICAL DATA SHEET

www.quadrios.de

Self Adjusting Wire-End Ferrule Crimping Pliers Range 0.25...10 mm² (AWG 23-7) Bundle Item-No.: 23T055


This crimping tool is particularly suitable for hobbyists, craftsmen, field service, service workshops, electronics technicians and laboratory needs. The crimping tool is optimally matched to the field of application and has an automatic adjustment to the sleeve diameters between 0.25 and 10 sqmm. The square crimping claw ensures a safe crimping process, the ergnonmic handle fits well in the hand and allows comfortable working. The pliers have an adjustment option for fine adjustment of the compressive force and a quick locking safety lock.



Technical Specifications

Four-mandrel press claw • Automatic adjustment • Fine adjustment ratchet pressure • Quick release safety lock • ergonomic handle • Range from 0.25 to 10 mm² (AWG 23 ... 7) • Weight: 363 g.

Usage example



Application by qualified electricians only.

Works best with Quadrios' ferrule assortment sets.





TECHNICAL DATA SHEET

www.quadrios.de

Ferrule assortment 1200 pcs (DIN color code) Bundle Item-No.: 23T055

These ferrules are especially suitable for hobbyists, craftsmen, field service, service workshops, electronics technicians and laboratory needs.

The assortment contains a 1200-piece premium ferrule set (DIN color code) for an application range of cable cross sections from 0.5 to 10 mm². Optimal for use with suitable wire end ferrule crimping pliers.





Technical Specifications

Voltage (max.): 440 V, Material: polyamide, copper alloy. The ferrules comply with RoHS directives and are CE compliant. Further technical data on the included components are noted in the data sheet. Installation by qualified electricians only.

Content

Practical assortment box, 25 ferrules yellow 6 qmm (10 AWG), 25 ferrules red 10 qmm (7 AWG), 50 ferrules grey 4 qmm (12 AWG), 250 ferrules blue 2,5 qmm (14 AWG), 250 ferrules black 1.5 qmm (16 AWG), 200 ferrules gray 0.75 qmm (20 AWG), 200 ferrules red 1 qmm (18 AWG), 200 ferrules white 0.5 qmm (22 AWG).